









ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F060602	LASEEV11
2	1		GREEN LENS
3	1	F051705	V3 FLUSH MOUNT RETAINER
4	1	F051704	V3 FLUSH MOUNT BEZEL
5	1	F050419	12VDC GREEN LED



NOTES:

- ALL DIMENSIONS IN MM [INCH].
- GENERAL TOLERANCE: x.x = ± 0.4
x.xx = ± 0.25
- TERM. NUMBERS FOR REF. ONLY.
- RATING: 5A @250VAC
8A @125VAC
0.2A @250VDC
6A @24VDC
- INSULATION: 1,000 MΩ MIN.
- DIELECTRIC STRENGTH: 2000V FOR 1 MIN.
- SEALED TO IP65.
- TRAVEL: 3.0mm FULL TRAVEL, 2.0mm LATCHING
- ELECTRICAL LIFE: >50,000 CYCLES
- OPERATING TEMP: -25C to +55C
- PANEL THICKNESS: 0.5mm TO 3.0mm
- ▲ 12. LAMP : GREEN LED; 12VDC
- ▲ 13. ▲ DENOTES CRITICAL PARAMETER
- ▲ 14. PACKAGE: BOX/10 PER



A	24209	RELEASED FOR PRODUCTION	3/2/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LASEEV31JGRNGRN

SCALE 1:1

DATE 3/2/2020

DR MW

DWG XF0929P

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[LASEEV31JGRNGRN](#)