



Figure similar

SIMATIC DP, DP/DP coupler Coupling module for connecting of two PROFIBUS DP networks redundant current infeed

| Supply voltage                            |        |
|-------------------------------------------|--------|
| Rated value (DC)                          | 24 V   |
| permissible range, lower limit (DC)       | 20.4 V |
| permissible range, upper limit (DC)       | 28.8 V |
| Input current                             |        |
| Current consumption, typ.                 | 90 mA  |
| Power loss                                |        |
| Power loss, typ.                          | 2 W    |
| Protocols                                 |        |
| PROFIBUS DP                               | Yes    |
| AS-Interface                              | No     |
| Interrupts/diagnostics/status information |        |
| Status indicator                          | Yes    |
| Diagnostics function                      | Yes    |
| Degree and class of protection            |        |
| IP degree of protection                   | IP20   |
| Ambient conditions                        |        |
| Ambient temperature during operation      |        |
| • min.                                    | 0 °C   |
| • max.                                    | 60 °C  |
| Dimensions                                |        |
| Width                                     | 40 mm  |
| Height                                    | 127 mm |
| Depth                                     | 117 mm |

last modified: 8/8/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71580AD010XA0](#)