



SIMATIC ET 200SP, BusAdapter BA 2xFC, 2x FastConnect connections

General information			
Product type designation	BA 2xFC		
Interfaces			
Number of PROFINET interfaces	1		
Supports protocol for PROFINET IO			
• Number of FC (FastConnect) connections	2		
Cable length			
— Cu conductors	100 m		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual		
Dimensions			
Width	20 mm		
Height	69.5 mm		
Depth	59 mm		
Weights			
Weight, approx.	53 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



[KC](#)



For use in hazardous locations



[FM](#)

[CCC-Ex](#)



[Miscellaneous](#)

Marine / Shipping



[NK / Nippon Kaiji Kyokai](#)



Marine / Shipping



[CCS \(China Classification Society\)](#)



last modified:

4/7/2025

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[6ES71936AF000AA0](#)