

SIMATIC DP, Connection module for PROFINET interface module, ET 200 PRO, connection 2xSCRJ FO 2x push-pull plug-in connectors for PROFINET PN



Figure similar

| Input current                              |                                                                      |
|--------------------------------------------|----------------------------------------------------------------------|
| from supply voltage 1L+, max.              | No current consumption, only infeed current, max. 16 A with derating |
| from load voltage 2L+ (without load), max. | No current consumption, only infeed current, max. 16 A with derating |
| Accessories                                |                                                                      |
| Function description                       | IM PN, 2x SCRJ FO, 2x PushPull interface module                      |
| belongs to product                         | IM154-4 PN HF                                                        |
| Dimensions                                 |                                                                      |
| Width                                      | 90 mm                                                                |
| Height                                     | 130 mm                                                               |
| Depth                                      | 51 mm                                                                |
| Weights                                    |                                                                      |
| Weight, approx.                            | 325 g                                                                |

last modified: 8/16/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71944AG000AA0](#)