



Figure similar

SIMATIC S7-1200, Digital input SB 1221, 4 DI, 24 V DC 200 kHz, Sourcing input

General information	
Product type designation	SB 1221, DI 4x24 V DC 200 kHz
Input current	
from backplane bus 5 V DC, typ.	40 mA
Power loss	
Power loss, typ.	1 W
Digital inputs	
Number of digital inputs	4; Current-sourcing
• in groups of	4
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	(L+ minus 5.0 V DC) ... L+ (1.4 ... 0 mA)
• for signal "1"	0 V ... (L+ minus 10 V DC (10 ... 2.9 mA))
Input current	
• for signal "0", max. (permissible quiescent current)	1.4 mA
• for signal "1", min.	2.9 mA
• for signal "1", typ.	7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 µs; 0.05 / 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 6.4 / 10.0 / 12.8 / 20.0 ms
for interrupt inputs	
— parameterizable	Yes
for technological functions	
— parameterizable	Yes
Cable length	
• shielded, max.	50 m; shielded, twisted pair
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• for status of the inputs	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes

Marine approval	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-20 °C
• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
Relative humidity	
• Operation at 25 °C without condensation, max.	95 %
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	
Width	38 mm
Height	62 mm
Depth	21 mm
Weights	
Weight, approx.	35 g

last modified: 8/16/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES72213BD300XB0](#)