

C FORM CONTACT 10A 1PC-VA402



| | |
|--|-----------------------------|
| design of the product | Aux Contacts |
| General technical data | |
| weight [lb] | 0.01 lb |
| Height x Width x Depth [in] | 1.54 × 0.87 × 0.4 in |
| ambient temperature [°F] | |
| • during storage | -67 ... +185 °F |
| • during operation | -40 ... +185 °F |
| ambient temperature | |
| • during storage | -55 ... +85 °C |
| • during operation | -40 ... +85 °C |
| Actuator | |
| mechanical service life (operating cycles) / typical | 10 000 000 |
| Contact block | |
| number of NC contacts / for auxiliary contacts | 1 |
| number of NO contacts / for auxiliary contacts | 1 |
| mechanical service life (operating cycles) / of auxiliary contacts / typical | 10 000 000 |
| Legend | |
| material | High strength thermoplastic |
| Mounting/wiring | |
| type of electrical connection | screw-type terminals |
| Certificates/ approvals | |
| certificate of suitability | cULus |
| Further information | |

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:CLM4097291>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:CLM4097291>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:CLM4097291&lang=en

last modified:

5/7/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

CLM4097291