



Figure similar

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. Type: ENCLOSED, SAFETY SWITCH Special Features: N/A Std: UL V. Rating: 1000VDC A. Rating: 200A No. Of Poles: 1P F. Rating: 60Hz Action: SINGLE THROW Closed Contact Resistance: N/A Connection: N/A

General technical data	
principle of operation of the actuating element	SINGLE THROW
mechanical service life (operating cycles) typical	8000
number of poles	1
Electricity	
ampacity	200 A
supply voltage frequency rated value 50/60 Hz	Yes
voltage between phase and phase rated value	1000 V
Environmental conditions	
ambient temperature during operation maximum	120 °C
ambient temperature during operation minimum	-20 °C
Model	
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
Mechanical Design	
design of the housing	TYPE 1
material	STEEL
General product approval	
certificate of suitability	UL

last modified:

9/15/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

HF1104NPV