



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 400A 3P 240V 3W FUSED HD TYPE 4X

General technical data	
fastening method	SURFACE
number of poles	3
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	400 A
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the actuating element	SINGLE THROW
material	304 STAINLESS STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/15/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

HF325SA