

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 30A 3P 600V  
3W FUSED HD T3R W/GB

| General technical data                             |   |
|--|---|
| mechanical service life (operating cycles) typical | 10000   |
| fastening method                                   | SURFACE   |
| number of poles                                    | 3   |
| suitability for operation                          | DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS |
| Electricity  |   |
| ampacity   | 30 A  |
| supply voltage frequency rated value 50/60 Hz      | Yes   |
| Environmental conditions                           |   |
| ambient temperature during operation maximum       | 85 °C   |
| ambient temperature during operation minimum       | -29 °C  |
| Model  |   |
| product brand name                                 | SIEMENS   |
| product sub brand name                             | VBII  |
| product type designation                           | HEAVY DUTY SWITCH                               |
| special product feature                            | FACTORY INSTALLED GROUND BAR                    |
| type of electrical connection                      | MECHANICAL LUGS                                 |
| Mechanical Design                                  |   |
| design of the housing                              | TYPE 3R   |
| design of the actuating element                    | SINGLE THROW                                    |
| material   | STEEL   |
| General product approval                           |   |
| certificate of suitability                         | UL98  |

last modified:

9/15/2021 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

HF361RG