

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. Type: ENCLOSED, SAFETY SWITCH Std: UL V. Rating: 240/600V A. Rating: 30-100A No. Of Poles: 2&3P F. Rating: 60Hz Action: SINGLE THROW. 2-3 point mounting holes. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
fastening method	2 OR 3 POINT MOUNTING HOLES
Electricity	
voltage between phase and Ground (GND) rated value	240 V
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
General product approval	
certificate of suitability	UL

last modified:

1/6/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

HH6123