



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 30A 2P 600V 2W NON-FUSED HD TYPE 12

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	2
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	30 A
supply voltage frequency rated value 50/60 Hz	Yes
Model	
product brand name	SIEMENS
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 3R/ 3S/ 12/ 13
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/16/2021 



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

HNF261J