

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 30A 2P 600V
2W NON-FUSED HD TYPE 3R



General technical data

mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	2
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS

Electricity

ampacity	30 A
supply voltage frequency rated value 50/60 Hz	Yes

Model

product brand name	SIEMENS
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS

Mechanical Design

design of the housing	TYPE 3R
design of the actuating element	SINGLE THROW
material	STEEL

General product approval

certificate of suitability	UL98
----------------------------	------

last modified:

9/16/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[HNF261R](#)