



Figure similar

Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL V. Rating: 600V A. Rating: 100A F. Rating: 60Hz Action: SINGLE THROW Enclosure: TYPE 1/3R/12 Mounting: FLANGE MOUNTING Insulation: YES O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDUSTRIAL/OUTDOOR

General technical data	
fastening method	FLANGE MOUNTING
Electricity	
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	OEM DISCONNECT SWITCH
General product approval	
certificate of suitability	UL
degree of protection NEMA rating	TYPE 1/3R/12

last modified: 1/6/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[MCS610R](#)