



Control Power Transformer, 50va, PRI 240x480 230x460 220 440v, SEC 120/115/110v, Domestic,

product brand name	Control Power Transformer
design of the product	Control power voltage
special product feature	Robust design
General technical data	
weight [lb]	3.5 lb
Height x Width x Depth [in]	3.46 × 3 × 3.64 in
ambient temperature [°F] during operation	-4 ... +104 °F
ambient temperature during operation	-20 ... +40 °C
country of origin	Mexico
operating apparent power rated value	50 VA
Enclosure	
design of the housing	Open
Mounting/wiring	
mounting position	Any
fastening method	Surface mounting
type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)
type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
Inputs/ Outputs	
input variables of primary voltage	240x480,230x460,220x440vac
output dimensions of secondary voltage	120/115/110vac
phase number of the inputs	1
electrical input frequency	50 ... 60 Hz
input voltage _1	240 V
input voltage _2	480 V
input voltage _3	230 V
input voltage _4	460 V
input voltage _5	220 V
input voltage _6	440 V
phase number of the outputs	1
electrical output frequency	60 ... 50 Hz
output voltage _1 rated value	120 V
output voltage _3 rated value	110 V
output voltage _2 rated value	115 V
certificate of suitability	UL / CSA
Further information	

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MT0050A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0050A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

last modified: 5/31/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[MT0050A](#)