



AS-i SlimLine Compact module SC22.5, IP20, analog, 4AI-RTD Screw terminals 4 x analog input Thermal resistance/resistor Overall width 22.5 mm

product designation	Slimline Compact I/O module for use in the control cabinet
design of the product	AS-i SC22.5, 4AI voltage/current
product type designation	3RK1
design of the slave type	standard slave
AS-Interface slave profile	S-7.3.E
ID1 code	F; Factory setting, changeable
operating voltage according to AS-Interface specification	18 ... 31.6 V
product function suitable for AS-i Power24V	Yes
consumed current from profile conductors of the AS-Interface	
• at 30 V maximum	100 mA
• at 24 V with AS-i Power24V maximum	100 mA
type of address setting of AS-i slaves	via front addressing socket
Substance Prohibitance (Date)	05/01/2012
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol - 119-47-1 Diboron trioxide - 1303-86-2
Weight	0.225 kg
reference code	
• according to EN 61346-2	K
• according to DIN 40719 extended according to IEC 204-2 according to IEC 750	A
shock resistance	15g / 11 ms (modules) or 10g / 11 ms (modules with device connector)
other information	An auxiliary external feed (AUX POWER) of between 20 and 30 V DC is necessary for supplying the output circuits. The auxiliary feed must comply with IEC 60990 (PELV), protection class III.
Digital Inputs	
number of digital inputs	0
number of digital inputs safety-related	0
Sensor supply	
type of voltage supply for sensor supply	using AS-Interface
Digital Outputs	
number of digital outputs	0
Analog inputs	
number of analog inputs	4
signal range at the analog input	Pt 100 standard and climate range / Ni 100 / resistance measurement 0 ... 600 Ohm
design of the sensor at the analog input is supported resistor temperature sensor	Yes
product function input variable parameterizable	Yes
A/D resolution for analog inputs/outputs	16 bit
product function smoothing parameterizable	Yes

set values of the interference frequency for interference voltage suppression	50 / 60 Hz
Analog outputs	
number of analog outputs	0
Errors/ accuracies	
relative symmetrical operational limit relating to input range/output range	1 %; full scale
relative symmetrical basic error limit relating to input range/output range at 25 °C	0.7 %
symmetrical temperature error per K relating to input range/output range	0.01 %/K
relative symmetrical linearity error relating to input range/output range	0.05 %
relative symmetrical repeat accuracy relating to input range/output range in settled state 25 °C	0.1 %
Device connector	
ampacity of the interface to the device connector	
• for AS-Interface	2 A
• for external auxiliary voltage	4 A
Installation/ mounting/ dimensions	
fastening method	screw and snap-on mounting
height	100 mm
width	22.5 mm
depth	120 mm
Ambient conditions	
ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
Connections/ Terminals	
type of electrical connection of the inputs and outputs	Screw terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1.5 mm²)
• finely stranded with core end processing	1x (0.25 ... 2.5 mm²), 2x (0.25 ... 1.0 mm²)
• finely stranded without core end processing	Not permitted
• for AWG cables solid	1x (24 ... 14), 2x (24 ... 16)
• for AWG cables stranded	Not permitted

Approvals Certificates

General Product Approval	EMV	Test Certificates
--------------------------	-----	-------------------



[Type Test Certificates/Test Report](#)

Marine / Shipping	other	Environment
-------------------	-------	-------------



[Confirmation](#)

[Environmental Confirmations](#)

Industrial Communication



Further information

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1207-3CE00-2AA2>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1207-3CE00-2AA2>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1207-3CE00-2AA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1207-3CE00-2AA2&lang=en





last modified:

4/2/2025 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK12073CE002AA2](#)