

		Energy connection cable single-sided, open on one side Han Q4/2 Han Q4/2 + jumper PIN 11+12 angled 5 x 4 mm2 Length 1.5 m
product brand name		SIRIUS
product designation		Power infeed cable
connector type		Pin
wire length	m	1.5
type of cable outlet		angled
number of electrical cores		5
number of poles		6
protection class IP		IP65
cable end components		One-sided
Further information		

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1911-0DC13>
Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1911-0DC13>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3RK1911-0DC13>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1911-0DC13&lang=en

last modified: 4/1/2025 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK19110DC13](#)