

Motor cable single-sided with brake without thermistor Brake 400 V
AC or 180 V DC Han Q8 - open on one side angled 6 x 1.5 mm²
Length 5 m

product brand name		SIRIUS
product designation		Motor cable
connector type		Pin
wire length	m	5
type of cable outlet		angled
number of electrical cores		6
number of poles		6
protection class IP		IP65
cable end components		One-sided

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1911-0ED31>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1911-0ED31>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1911-0ED31>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1911-0ED31&lang=en

last modified:

12/23/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK19110ED31](#)