



Figure similar

ECOFAST hybrid field connection PROFIBUS CU/CU signal refresher CU socket/socket IP65 frond side CU D-SUB 9-pole Socket inside active (signal refresher) Automatic baud rate search

General technical data					
Substance Prohibittance (Date)		07/01/2006			
Weight		0.303 kg			
Approvals Certificates					
General Product Approval		EMV	other	Environment	
 EG-Konf.	 UL		 RCM	Confirmation	Environmental Confirmations

Further information	
Information on the packaging	
https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information- and Downloadcenter (Catalogs, Brochures,...)	
https://www.siemens.com/ic10	
Industry Mall (Online ordering system)	
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1911-1AJ22	
Cax online generator	
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1911-1AJ22	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
https://support.industry.siemens.com/cs/ww/en/ps/3RK1911-1AJ22	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1911-1AJ22&lang=en	

last modified: 4/2/2025 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK19111AJ22](#)