



ECOFAST fieldbus connection PROFIBUS CU/CU signal refresher Front side 2 x M12 Socket/socket IP65 frond side CU D-SUB 9-pole Socket inside active (signal refresher) Automatic baud rate search

General technical data			
Substance Prohibittance (Date)	07/01/2006		
Weight	0.246 kg		
Approvals Certificates			
General Product Approval	EMV	other	Environment
 EG-Konf.	 UL		 RCM
		Confirmation	Environmental Confirmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1911-1AK22
Cax online generator http://support.automation.siemens.com/VW/CAXorder/default.aspx?lang=en&mlfb=3RK1911-1AK22
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RK1911-1AK22
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1911-1AK22&lang=en

last modified: 4/2/2025 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK19111AK22](#)