



AS-i SlimLine module Phased-out product !!! For further information, please contact our sales department S45 digital, A/B slave 4 DI/4 DQ, IP20 4 x inputs for 3-wire sensor 4 x output, 2 A, 24 V DC maximal 4 A for all outputs Screw terminals Overall width 45 mm

General technical data		
design of the product		SlimLine S22.5 - I/O modules for operation in the control cabinet
design of the slave type		A/B slave (Spec. 3.0)
Type		4 inputs / 4 outputs
I/O configuration		7
ID/ID2 code		A/7
protocol is supported AS-Interface protocol		Yes
AS interface total current input max	mA	270
operating voltage according to AS-Interface specification	V	26.5 ... 31.6
Addressing		front addressing socket
type of electrical connection of the inputs and outputs		screw-type terminals
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750		A
reference code according to EN 61346-2		K
note		An external additional supply (AUX POWER) of 20 to 30 V DC is required for the supply of the output circuits. The additional supply must comply with VDE 0106 (PELV), protection class III.
Sensor supply		
type of voltage supply for sensor supply		using AS-Interface
input voltage	V	20 ... 30
property of the sensor supply short-circuit and overload resistant		Yes
ampacity of the sensor supply for all inputs		
• at ambient temperature 40 °C	mA	200
Inputs		
number of digital inputs		4
type of connection technology		2- and 3-wire technology
Input circuit		PNP transistor
type of voltage of the input voltages		DC
Inputs switching level High min	V	10
input current at digital input		
• for signal <1> minimum	A	5
• with signal <0> maximum	mA	1.5
Inputs sensor supply using AS-Interface		short-circuit and overload resistant
Outputs		
number of digital outputs		4
type of voltage of output voltages		DC
output voltage at DC at 24 V	V	22 ... 24
Outputs external power supply 24 V DC		using terminals: Terminal 13 = L+, Terminal 19 = M
Outputs		
• aggregate current max	A	4

ampacity • of the semiconductor output at DC-13 at 24 V	A	2
type of switching output		solid state
property of the output short-circuit proof		Yes
output Polarity reversal protection		built-in
Outputs • short-circuit protection • induction protection • watchdog		built-in built-in built-in
Status display • display of I/Os • AS-Interface • FAULT		yellow LED green LED red LED
Assignment of data bits • D0 • D1 • D2 • D3		IN1/OUT1 IN2 /OUT2 IN3/OUT3 IN4/OUT4

Ambient conditions

ambient temperature • during operation • during storage	°C °C	-25 ... +70 -40 ... +85
protection class IP		IP20

Mechanical data

width	mm	45
height	mm	106
depth	mm	86
fastening method		35 mm standard rail mounting or wall mounting using push-in lugs
Conductor cross-section • solid • finely stranded — with end sleeve • AWG solid or stranded		1 x (0.5 - 4) mm ² or 2 x (0.5 - 2.5) mm ² 1 x (0.5 - 2.5) mm ² or 2 x (0.5 - 1.5) mm ² AWG 2 x (20 - 14) mm ²

Certificates/ approvals

General Product Approval	EMV
---------------------------------	-----



[KC](#)

Marine / Shipping	other	Environment	Industrial Communication
--------------------------	--------------	--------------------	---------------------------------



[Confirmation](#)

[Miscellaneous](#)

[Environmental Con-
firmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK2400-1CE01-0AA2>

Cax online generator



<http://support.automation.siemens.com/VW/CAXorder/default.aspx?lang=en&mlfb=3RK2400-1CE01-0AA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK2400-1CE01-0AA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK2400-1CE01-0AA2&lang=en



last modified:

3/11/2024 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK24001CE010AA2](#)