



surge suppressor, RC element, 127-240 V AC, 50/60 Hz, 150-250 V DC, for contactors 3RT2.4

|   |                  |     |                                |
|---|------------------|-----|--------------------------------|
| product brand name                            | SIRIUS           |     |                                |
| product designation                           | surge suppressor |     |                                |
| General technical data                        |                  |     |                                |
| size of contactor                             | S3               |     |                                |
| certificate of suitability                    | CE / UL / CSA    |     |                                |
| Substance Prohibitance (Date)                 | 07/01/2006       |     |                                |
| type of voltage of the control supply voltage | AC/DC            |     |                                |
| control supply voltage 1 at AC                |                  |     |                                |
| • at 50 Hz                                    | 127 ... 240 V    |     |                                |
| • at 60 Hz                                    | 127 ... 240 V    |     |                                |
| control supply voltage frequency              |                  |     |                                |
| • 1 rated value                               | 50 Hz            |     |                                |
| • 2 rated value                               | 60 Hz            |     |                                |
| control supply voltage 1                      |                  |     |                                |
| • at DC                                       | 150 ... 250 V    |     |                                |
| design of the surge suppressor                | RC element       |     |                                |
| Ambient conditions                            |                  |     |                                |
| ambient temperature                           |                  |     |                                |
| • during operation                            | -25 ... +60 °C   |     |                                |
| • during storage                              | -40 ... +80 °C   |     |                                |
| Installation/ mounting/ dimensions            |                  |     |                                |
| height  | 55 mm            |     |                                |
| width   | 25 mm            |     |                                |
| depth   | 23 mm            |     |                                |
| Approvals Certificates                        |                  |     |                                |
| General Product Approval                      |                  | EMC | Declaration of Con-<br>formity |



[Confirmation](#)



EG-Konf.

|                                |  |                   |       |                              |
|--------------------------------|--|-------------------|-------|------------------------------|
| Declaration of Con-<br>formity | Test Certificates                                  | Marine / Shipping | other |                              |
|                                | <a href="#">Type Test Certificates/Test Report</a> |                   |       |                              |
|                                |  |                   |       | <a href="#">Confirmation</a> |

## Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2946-1CD00>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2946-1CD00>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2946-1CD00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT2946-1CD00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2946-1CD00&lang=en)





---

last modified:

10/22/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RT29461CD00](#)