



Undervoltage release 400 V AC/50 Hz, 440 V AC/60 Hz with ring cable lug connection for circuit breaker 3RV2

product brand name	SIRIUS
product designation	undervoltage release
suitability for use	motor circuit breaker
General technical data	
size of the circuit-breaker	S00, S0, S2, S3
closing active power at AC maximum	13 W
active power at AC in operation maximum	2.4 W
apparent power at AC in operation maximum	7.2 VA
insulation voltage	
• rated value	690 V
• with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
break time maximum	20 ms
certificate of suitability	CE / UL / CSA
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750	F
reference code according to EN 61346-2	F
Substance Prohibitance (Date)	05/01/2012
type of voltage of the control supply voltage	AC
control supply voltage 1 at AC	
• at 50 Hz rated value	400 V
• at 60 Hz rated value	440 V
control supply voltage frequency 1	50 ... 60 Hz
number of NC contacts for auxiliary contacts instantaneous contact	0
number of NO contacts for auxiliary contacts	
• instantaneous contact	0
• leading contact	0
number of CO contacts of auxiliary contacts instantaneous contact	0
Ambient conditions	
ambient temperature	
• during operation	-20 ... +60 °C
• during storage	-50 ... +80 °C
Safety related data	
protection class IP on the front according to IEC 60529	IP00
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Short-circuit protection	
design of short-circuit protection	fuse
Installation/ mounting/ dimensions	
fastening method	snap-on mounting

height	90 mm	
width	19 mm	
depth	68 mm	
Connections/ Terminals		
type of electrical connection for auxiliary and control circuit	ring terminal lug connection	
Approvals Certificates		
General Product Approval	Declaration of Conformity	Test Certificates
Confirmation	   	Special Test Certificate
Test Certificates	Marine / Shipping	
Type Test Certificates/Test Report	    	
Marine / Shipping	other	Railway
 Confirmation 	Vibration and Shock	

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2902-4AV0>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2902-4AV0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2902-4AV0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2902-4AV0&lang=en





last modified:

5/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RV29024AV0](#)