

3-phase busbar including extension connector for 2 circuit breakers Size S00 and S0

product brand name	SIRIUS
product designation	three-phase busbars for system expansion
design of the product	for 2 switches
suitability for use	circuit-breakers 3RV2
General technical data	
size of the circuit-breaker	S00, S0
surge voltage resistance rated value	6 kV
thermal current	63 A
certificate of suitability	CE / UL / CSA / CCC
Substance Prohibition (Date)	10/01/2009
number of poles for main current circuit	3
operating voltage at AC rated value	500 V
operational current rated value	63 A
UL/CSA ratings	
operating voltage at AC according to UL rated value	600 V
Ambient conditions	
ambient temperature during operation	-20 ... +60 °C
Safety related data	
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Short-circuit protection	
short-circuit rating	corresponds to the installed circuit breaker or load feeder
Installation/ mounting/ dimensions	
mounting position	any
fastening method	snap-on fastening on 35 mm DIN rail
height	129 mm
width	91.4 mm
depth	58.5 mm
required spacing	
• with side-by-side mounting	
— backwards	0 mm
— upwards	10 mm
— at the side	0 mm
• for grounded parts	
— backwards	0 mm
— upwards	10 mm
— at the side	0 mm
• for live parts	
— backwards	0 mm
— upwards	10 mm

— at the side

0 mm

Connections/ Terminals

type of electrical connection for main current circuit

plug-in without terminals

Approvals Certificates

General Product Approval

Declaration of Conformity

Test Certificates

[Confirmation](#)



[Special Test Certificate](#)

Test Certificates

Marine / Shipping

[Type Test Certificates/Test Report](#)



Marine / Shipping

other

Railway



[Confirmation](#)



[Vibration and Shock](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2917-4A>

Cax online generator




<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2917-4A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2917-4A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2917-4A&lang=en



last modified:

7/6/2023

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RV29174A