



Figure similar

AS-i Power 3 A 24 V DC AS-Interface power supply unit, IP20 IN: 24 V DC OUT: AS-i, 3 A (30 V DC), IP20 with integrated ground fault detection, with integrated overload detection with AS-i data decoupling

General technical data		
Type of device		AS-Interface power supply unit IP20
version		single output
Additional function		integrated ground-fault detection, remote reset and remote indication
input voltage at DC	V	24
Inputs		
input voltage at DC	V	20 ... 29
input		- Mains buffering time at I_a rated min 10 ms - input voltage built-in T 8 (not accessible)
Connections input		spring-loaded terminal connection input (0.2 ... 2.5 mm ²)/diagnosis (0.14 ... 1.5 mm ²)
Outputs		
output		- DC-voltage controlled floating according to AS-Interface specification yes - voltage rated value U_a rated DC 30 V - tolerance total DC V 29.5 ... 31.6 - rated current I_a rated 3 A - residual ripple peak-to-peak (0-10 kHz, AS-i+/AS-i-) max mV 300 - spikes peak-to-peak (10-500 kHz, AS-i+/AS-i-) max mV 50
Connections Output		spring-loaded terminal connection output (0.2 ... 2.5 mm ²)/diagnosis (0.14 ... 1.5 mm ²)
Efficiency/ heat loss		
Efficiency at U _a rated, I _a rated	%	84
power loss [W] maximum	W	17.8
Protective and monitoring functions		
Output overvoltage protection		yes (< 35V)
Current limitation from min.		3.5 A
Short-circuit protection		yes
Safety related data		
protection class (EN 60 950/IEC 950)		III
Electrical isolation primary/secondary		ES1 according EN 62368-1 (for products until end of 2020: SELV according to EN 60 950 and EN 50 178)
protection class IP		IP20
Electromagnetic compatibility		
electromagnetic compatibility (EMC)		- interference immunity EN 61 000-6-2, EN 61 000-4-2/-3/-4/-5/-11 - emitted interference class B according to EN 55 022, IEC 61 000-6-3

Ambient conditions		
ambient temperature	°C	-10 ... +70
	°C	-25 ... +80
humidity rating		climatic class DIN 50010, relative humidity max. 100% without condensation
fastening method		fixing on standard mounting rail DIN EN 59 022-35 x 7.5 mm snap-on
width	mm	50
height	mm	125
depth	mm	125
Certificates/ approvals		
General Product Approval		



[Confirmation](#)



EG-Konf.



UL



EMV	Marine / Shipping	other
-----	-------------------	-------



RCM

[KC](#)



DNV



LRS



PRS

[Confirmation](#)

other	Environment	Industrial Communication
-------	-------------	--------------------------

[Miscellaneous](#)



[Environmental Confirmations](#)



ASi

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RX9501-1BA00>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RX9501-1BA00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RX9501-1BA00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RX9501-1BA00&lang=en



last modified:

4/23/2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RX95011BA00](#)