



Figure similar

Lampholder, Wedge base W2 x 4.6 d, with incandescent lamp 24 V, with holder

product brand name	SIRIUS
product designation	lampholder
product type designation	3SB2
Contact block/ lampholder	
socket design	W2 x 4.6d
number of lampholders	1
General technical data	
product function EMERGENCY STOP function	No
product component	
• diode	No
• lamp transformer	No
• light source	Yes
• series resistor	No
suitability for integration	front element
protection class IP	
• of the enclosure	IP00
• of the terminal	IP00
vibration resistance according to IEC 60068-2-6	20 ... 200 Hz: 5g
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	07/01/2006
operating voltage	
• at AC	
— at 50 Hz rated value	5 ... 60 V
— at 60 Hz rated value	5 ... 60 V
• at DC rated value	5 ... 60 V
Supply voltage	
type of voltage of the supply voltage of the light source	AC/DC
supply voltage of the light source at AC	
• at 50 Hz rated value	24 V
• at 60 Hz rated value	24 V
supply voltage 1 of the light source at DC rated value	24 V
relative negative tolerance of the supply voltage	-15 %
relative positive tolerance of the supply voltage	10 %
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
operational current at DC-13	
• at 24 V rated value	3 A

Connections/ Terminals	
type of electrical connection	tab terminals
Lamp	
type of light source	filament lamp
color of the light source	clear
Ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
Installation/ mounting/ dimensions	
fastening method	front plate mounting
height	19 mm
width	19 mm
depth	46 mm
Approvals Certificates	
General Product Approval	



other	Environment
-------	-------------

[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2304-2H>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2304-2H>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2304-2H>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2304-2H&lang=en

last modified:

1/27/2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3SB23042H](#)