



incandescent lamp, clear, rated voltage 60 V AC/DC, 1.0 W, Wedge base W2 x 4.6 d,

Figure similar

| General technical data                                     |    |                   |
|------------------------------------------------------------|----|-------------------|
| product designation                                        |    | incandescent lamp |
| type of light source                                       |    | filament lamp     |
| color of the light source                                  |    | clear             |
| socket design                                              |    | W2 x 4.6d         |
| product component                                          |    |                   |
| • series resistor                                          |    | No                |
| • diode                                                    |    | No                |
| • lamp transformer                                         |    | No                |
| • light source                                             |    | Yes               |
| type of voltage of the operating voltage for actuation     |    | AC/DC             |
| operating voltage                                          |    |                   |
| • at AC                                                    |    |                   |
| — at 50 Hz rated value                                     | V  | 60 ... 60         |
| — at 60 Hz rated value                                     | V  | 60 ... 60         |
| • at DC rated value                                        | V  | 60 ... 60         |
| consumed current for rated value of supply voltage maximum | mA | 25                |
| type of electrical connection                              |    | Miscellaneous     |
| fastening method                                           |    | miscellaneous     |

Certificates/ approvals

| General Product Approval                                                                                                                                                                                                                                                                                                                                                                                                                     | Test Certificates             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|
| <div></div> | <a href="#">Miscellaneous</a> |

other

[Confirmation](#)

Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2908-1AF>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2908-1AF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2908-1AF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2908-1AF&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2908-1AF&lang=en)

---

last modified:

12/23/2020 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3SB29081AF](#)