

ACCESSORY / SPARE PART ROUND, 22MM/SQUARE, 26X26MM: LED SUPER-BRIGHT LAMPS, WEDGE-BASE WEDGE-BASE W2 X 4.6D RATED VOLTAGE 24V AC/DC OPERATIONAL CURRENT 10 MA YELLOW



Figure similar

General technical data		
product designation		LED lamp, super bright
type of light source		LED
color of the light source		yellow
socket design		W2 x 4.6d
product component		
• series resistor		No
• diode		No
• lamp transformer		No
• light source		Yes
type of voltage of the operating voltage for actuation		AC/DC
operating voltage		
• at AC		
— at 50 Hz rated value	V	24 ... 24
— at 60 Hz rated value	V	24 ... 24
• at DC rated value	V	24 ... 24
relative positive tolerance of the operating voltage	%	10
relative negative tolerance of the operating voltage	%	-15
consumed current for rated value of supply voltage maximum	mA	10
type of electrical connection		Miscellaneous
fastening method		miscellaneous
Certificates/ approvals		
General Product Approval	other	



[Confirmation](#)

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB3901-1RB
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB3901-1RB
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SB3901-1RB
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

last modified:

1/8/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3SB39011RB](#)