SIEMENS

## Data sheet 3SU1030-5HF01-0AA0-Z Y19

key-operated switch Siemens, 22 mm, round, plastic with metal front ring, lock no. LSG1, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, key removal O, with laser labeling, inscription or symbol customer-specific selection with SIRIUS ACT configurator (CIN)

| | |
|---|---|
| **product brand name** | SIRIUS ACT |
| **product designation** | Key-operated switches |
| **design of the product** | Actuating/signaling element |
| **product type designation** | 3SU1 |
| **product line** | Plastic with metal front ring, matt, 22 mm |
| **manufacturer's article number of included key** | 3SU1950-0FN80-0AA0 |
| **Actuator** | |
| **principle of operation of the actuating element** | latching, 90° (10:30 h/13:30 h) |
| product extension optional light source | No |
| **color** | |
| ● of the actuating element | silver |
| **material of the actuating element** | metal |
| **shape of the actuating element** | Key |
| **outer diameter of the actuating element** | 29.5 mm |
| **marking of the actuating element** | Customized labeling, text or symbols, can only be ordered via SIRIUS ACT configurator/Configuration Identification Number (CIN) |
| **number of switching positions** | 2 |
| **switch position for key distraction** | O |
| **actuating angle** | |
| ● clockwise | 90° |
| **lock make** | Siemens |
| **key number** | LSG1 |
| **Front ring** | |
| **product component front ring** | Yes |
| **design of the front ring** | Standard |
| **material of the front ring** | Metal, matt |
| **color of the front ring** | sand gray |
| **General technical data** | |
| **protection class IP** | IP66, IP67, IP69(IP69K) |
| ● of the terminal | IP20 |
| **degree of protection NEMA rating** | 1, 2, 3, 3R, 4, 4X, 12, 13 |
| **shock resistance** | |
| ● **according to IEC 60068-2-27** | sinusoidal half-wave 15g / 11 ms |
| ● for railway applications according to EN 61373 | Category 1, Class B |
| **vibration resistance** | |
| ● **according to IEC 60068-2-6** | 10 ... 500 Hz: 5g |
| ● for railway applications according to EN 61373 | Category 1, Class B |
| **operating frequency maximum** | 1 800 1/h |
| **mechanical service life (operating cycles) typical** | 1 000 000 |
| **reference code according to IEC 81346-2** | S |


Subject to change without notice
© Copyright Siemens

| | |
|---|---|
| **Substance Prohibitance (Date)** | 10/01/2014 |
| **Ambient conditions** | |
| **ambient temperature** | |
| ● during operation | -25 ... +70 °C |
| ● during storage | -40 ... +80 °C |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| **Installation/ mounting/ dimensions** | |
| **height** | 29.5 mm |
| **width** | 29.5 mm |
| **shape of the installation opening** | round |
| **mounting diameter** | 22.3 mm |
| **positive tolerance of installation diameter** | 0.4 mm |
| **mounting height** | 61 mm |
| **installation width** | 29.5 mm |
| **installation depth** | 25.4 mm |

**Approvals Certificates**

**General Product Approval**

Confirmation

**Test Certificates**

Type Test Certific-ates/Test Report

Special Test Certific-ate

**Marine / Shipping**

**other**

Confirmation

**Environment**

Environmental Con-firmations

**Further information**

**Information on the packaging**
https://support.industry.siemens.com/cs/ww/en/view/109813875
**Information- and Downloadcenter (Catalogs, Brochures,…)**
https://www.siemens.com/ic10
**Industry Mall (Online ordering system)**
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1030-5HF01-0AA0-Z Y19
**Cax online generator**
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1030-5HF01-0AA0-Z Y19
**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
https://support.industry.siemens.com/cs/ww/en/ps/3SU1030-5HF01-0AA0-Z Y19
**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1030-5HF01-0AA0-Z Y19&lang=en

**last modified:** 3/2/2024


Subject to change without notice
© Copyright Siemens

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

A6X30138166