

## Data sheet

## 3SU1050-0AA10-0AA0-Z Y10



Pushbutton, 22 mm, round, metal, shiny, black, pushbutton, flat, latching, Push-to-release mechanism, with laser labeling, upper case and lower case, always upper case at beginning of line

|  |  |
|--|--|
| product brand name                                 | SIRIUS ACT   |
| product designation                                | Pushbuttons  |
| design of the product                              | Actuating/signaling element  |
| product type designation                           | 3SU1   |
| product line                                       | Metal, shiny, 22 mm  |
| <b>Enclosure</b>                                   |  |
| number of command points                           | 1  |
| <b>Actuator</b>                                    |  |
| design of the actuating element                    | Flat button  |
| principle of operation of the actuating element    | latching   |
| product extension optional                         |  |
| • light source                                     | No   |
| • contact module                                   | Yes  |
| color of the actuating element                     | black  |
| material of the actuating element                  | plastic  |
| shape of the actuating element                     | round  |
| outer diameter of the actuating element            | 29.5 mm  |
| marking of the actuating element                   | Customized labeling, text in lower case / capital letters, all lines start with capital letter |
| type of unlocking device                           | push-to-unlatch mechanism  |
| <b>Front ring</b>                                  |  |
| product component front ring                       | Yes  |
| design of the front ring                           | Standard   |
| material of the front ring                         | Metal, high gloss  |
| color of the front ring                            | silver   |
| <b>General technical data</b>                      |  |
| protection class IP                                | IP66, IP67, IP69(IP69K)  |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13   |
| shock resistance                                   |  |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms   |
| vibration resistance                               |  |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g  |
| operating frequency maximum                        | 1 800 1/h  |
| mechanical service life (operating cycles) typical | 500 000  |
| reference code according to IEC 81346-2            | S  |
| Substance Prohibitance (Date)                      | 10/01/2014   |
| <b>Ambient conditions</b>                          |  |
| ambient temperature                                |  |
| • during operation                                 | -25 ... +70 °C   |
| • during storage                                   | -40 ... +80 °C   |

|  |  |
|--|--|
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| <b>Installation/ mounting/ dimensions</b>                      |  |
| height   | 29.5 mm  |
| width  | 29.5 mm  |
| shape of the installation opening                              | round  |
| mounting diameter  | 22.3 mm  |
| positive tolerance of installation diameter                    | 0.4 mm   |
| mounting height  | 11 mm  |
| installation width   | 29.5 mm  |
| installation depth   | 24.3 mm  |

|                            |
|----------------------------|
| <b>Further information</b> |
|----------------------------|

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-0AA10-0AA0-Z Y10>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAxorder/default.aspx?lang=en&mlfb=3SU1050-0AA10-0AA0-Z Y10>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-0AA10-0AA0-Z Y10>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-0AA10-0AA0-Z Y10&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-0AA10-0AA0-Z Y10&lang=en)

last modified:

1/26/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30138820](#)