











LED module with integrated LED 230 V AC, amber, spring-type terminal, for floor mounting

product brand name	SIRIUS ACT
product designation	LED module
product type designation	3SU1
General technical data	
product component	
• diode	Yes
• lamp transformer	No
• light source	Yes
• series resistor	No
insulation voltage rated value	320 V
degree of pollution	3
type of voltage of the operating voltage	AC
• for actuation	AC
surge voltage resistance rated value	4 kV
consumed current maximum	20 mA
protection class IP	
• of the enclosure	IP40
• of the terminal	IP20
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating period typical	100 000 h
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	10/01/2014
operating voltage 1	
• at AC	
— at 50 Hz rated value	230 V
— at 60 Hz rated value	230 V
relative positive tolerance of the operating voltage	20 %
relative negative tolerance of the operating voltage	20 %
Control circuit/ Control	
inrush current maximum	3 A
Connections/ Terminals	
type of electrical connection	spring-loaded terminals
type of connectable conductor cross-sections	
• solid without core end processing	2x (0.25 ... 1.5 mm ²)
• finely stranded with core end processing	2x (0.25 ... 0.75 mm ²)

<ul style="list-style-type: none"> finely stranded without core end processing for AWG cables 	2x (0.25 ... 1.5 mm ²) 2x (24 ... 16)		
Lamp			
type of light source	LED		
color of the light source	amber		
light intensity	450 ... 1 120 mcd		
certificate of suitability			
<ul style="list-style-type: none"> ATEX IECEx 	No No		
Ambient conditions			
ambient temperature			
<ul style="list-style-type: none"> during operation during storage 	-25 ... +70 °C -40 ... +80 °C		
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)		
Installation/ mounting/ dimensions			
fastening method			
<ul style="list-style-type: none"> of modules and accessories 	Floor mounting		
height	36 mm		
width	9.8 mm		
depth	29.4 mm		
suitability for integration			
<ul style="list-style-type: none"> plastic enclosure metal enclosure 	Yes Yes		
Certificates/ approvals			
<table> <tr> <td>General Product Approval</td><td>Declaration of Conformity</td></tr> </table>		General Product Approval	Declaration of Conformity
General Product Approval	Declaration of Conformity		
<div> Confirmation      </div>			
<table> <tr> <td>Test Certificates</td><td>Marine / Shipping</td></tr> </table>		Test Certificates	Marine / Shipping
Test Certificates	Marine / Shipping		
<div> Special Test Certificate Type Test Certificates/Test Report     </div>			
<table> <tr> <td>other</td><td>Environment</td></tr> </table>		other	Environment
other	Environment		
<div> Confirmation Environmental Confirmations </div>			
Further information			
<p>Siemens has decided to exit the Russian market (see here). https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business</p> <p>Siemens is working on the renewal of the current EAC certificates. Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).</p> <p>Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875</p> <p>Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10</p> <p>Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1401-2BF00-3AA0</p> <p>Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1401-2BF00-3AA0</p> <p>Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SU1401-2BF00-3AA0</p> <p>Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1401-2BF00-3AA0&lang=en</p>			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3SU14012BF003AA0](#)