

connection cable 8-pole bare cable end, 3 m long, straight socket M12, for 2 A and 30 V



General technical data	
product brand name	SIRIUS
product designation	connection cable, socket 8-pole, 3 m
operational current at 40 °C rated value	2 A
operating voltage rated value	30 V
number of poles	8
insulation resistance	100 MΩ
wire length of connection cable	3 m
stripped length	50 mm
ambient temperature during operation	-25 ... +90 °C
connector coding of the M12 circular connector	A - Standard
type of electrical connection	connector M12
color coding of the core	Pin 1 = WH, Pin 2 = BN, Pin 3 = GN, Pin 4 = YE, Pin 5 = GY, Pin 6 = PK, Pin 7 = BU, Pin 8 = RD; (DIN 47100)
overvoltage category	2
degree of pollution	3
protection class IP	IP68
material	
• of the contact	CuZn
• of contact coating	Ni/Au
• of contact main body	TPU GF
• of the sealing ring	NBR

Certificates/ approvals		
General Product Approval	Declaration of Conformity	other

[Confirmation](#)



[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>



Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SX5601-2GA03>

Cax online generator



1	WH = White
2	BN = Brown
3	GN = Green
4	YE = Yellow
5	GY = Grey
6	PK = Pink
7	BU = Blue
8	RD = Red

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3SX56012GA03