

Wire connector TC1.4 6 AWG...350 kcmil Cu with control wire voltage tap-off 4 units accessories for: 3VA5 250



Model	
product brand name	SETRON
product designation	accessories
design of the product	circular conductor terminal
accessories	Wire connector
General technical data	
designation / of the terminal	TC1.4
type of electrical connection / with control wire tap	Yes
Connections according IEC	
stripped length	20 mm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C
stripped length	0.8 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	6 AWG
• for copper cable / stranded / maximum	350 kcmil
• for copper cable / finely stranded / minimum	6 AWG
• for copper cable / finely stranded / maximum	350 kcmil
tightening torque / when using copper cables	
• stranded	6 - 2 AWG: 140 lb-in, 1 AWG - 350 kcmil: 275 lb-in
• finely stranded	6 - 2 AWG: 140 lb-in, 1 AWG - 350 kcmil: 275 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9234-0JK12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9234-0JK12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9234-0JK12

CAX-Online-Generator


<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/15/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA92340JK12](#)