



Wire connector TA2.7 6 x 14 AWG...2 AWG for 6 cables 3 units; incl. terminal cover extended with holes for voltage test; accessories for: 3VA5/6 400/600 plug-in/draw-out socket 3VA5/6 400/600

Model	
product brand name	SETRON
product designation	accessories
design of the product	circular conductor terminal 6 cables 3 units
accessories	Wire connector
General technical data	
designation / of the terminal	TA2.7
type of electrical connection / with control wire tap	No
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	1.5 mm ²
• for copper cable / stranded / maximum	35 mm ²
stripped length	18 / 34,5 mm
tightening torque / when using copper cables	
• solid	1.5 mm ² : 2.8 Nm, 2.5 - 10 mm ² : 6.2 Nm 16 mm ² : 7 Nm
• stranded	1.5 mm ² : 2.8 Nm 2.5 - 10 mm ² : 6.2 Nm 16 - 35 mm ² : 7 Nm
• finely stranded	1.5 mm ² : 2.8 Nm, 2.5 - 10 mm ² : 6.2 Nm 16 - 25 mm ² : 7 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	0.7 / 1.35 in
connectable conductor cross-section	
• for copper cable / solid / minimum	14 AWG
• for copper cable / solid / maximum	10 AWG
• for copper cable / stranded / minimum	14 AWG
• for copper cable / stranded / maximum	2 AWG
• for copper cable / finely stranded / minimum	14 AWG
• for copper cable / finely stranded / maximum	2 AWG
• for aluminum cable / solid / minimum	12 AWG
• for aluminum cable / solid / maximum	10 AWG
• for aluminum cable / stranded / minimum	12 AWG
• for aluminum cable / stranded / maximum	2 AWG
tightening torque / when using copper cables	
• solid	12 - 10 AWG: 55 lb-in,
• stranded	14 - 8 AWG: 55 lb-in 6 - 2 AWG: 62 lb-in
• finely stranded	14 - 8 AWG: 55 lb-in 6 - 2 AWG: 62 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an

EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JF68>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JF68>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)





http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JF68

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/1/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA93730JF68](#)