



Figure similar

SIRIUS SIMOCODE ES V15.1 Premium, upgrade for SIMOCODE ES 2007, Floating License for one user Engineering software, SW+docum. on DVD License key on USB, Class A, 6 languages (de,en,it,fr,sp,cn) Combo License parallel use of SIMOCODE ES 2007 and V15 for SIMOCODE pro, online functions via system interface and PROFIBUS / PROFINET, Int. graphic editor (CFC-based) Executable in: Win 7 SP1 / Win 10 - 64-bit (Prof./Ultimate/Enterprise) / Win Server 2012 R2 StdE / 2016 - 64-bit Content: set (1xDVD + 1x USB)

General technical data		
product designation		SIMOCODE ES (TIA Portal)
software version		V 15
product description		Engineering software for SIMOCODE pro 3UF7; for all SIMOCODE pro; combo license for parallel use of versions 2007 and V15 of SIRIUS ES; online functions via system interface and PROFIBUS/PROFINET; parameter assignment via integrated graphic editor (CFC-based); license key on USB flash drive
national language of the software		German / English / French / Italian / Spanish / Chinese
product variations		Premium
product license		floating license for 1 user
processor clock frequency		
• minimum	MHz	3 400
operating system required		Microsoft Windows 7 SP1 64-bit Professional / Ultimate / Enterprise; Microsoft Windows 10 64-bit Pro / Enterprise; Microsoft Windows Server 2012 64-bit R2 StdE; Microsoft Windows Server 2016 64-bit
software class		A
target system		SIMOCODE pro 3UF7
Features		
product component component library		No
• product function diagnostics function		Yes
• product function controlled positioning		No
• product function simulation function		No
• product function technological function		No
• product function analysis function		Yes
• product function movement function		No
• product function data acquisition function		Yes
• product function commissioning function		Yes
• product function communication function		Yes
• product function project planning function		Yes
• Product function maintenance function		Yes
• product function evaluation function		Yes
• product function parameterizing function		Yes
Requirements		
storage capacity		
• on hard disk required	Mbyte	50
• of the main memory or RAM minimum	Mbyte	16
design of the drive/storage medium required		

• CD-ROM		No
• floppy disk		No
• DVD drive		Yes
Graphics card		
vertical image resolution of the graphics card	pixel	1 080
horizontal image resolution of the graphics card	pixel	1 920
number of colors of the graphics card		16 780 000
Software		
browser software required		no
viewer software required		no
Certificates/ approvals		
other		

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3ZS1322-6CC13-0YE5>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3ZS1322-6CC13-0YE5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3ZS1322-6CC13-0YE5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3ZS1322-6CC13-0YE5&lang=en

last modified:

12/23/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3ZS13226CC130YE5](#)