




Figure similar

TRANSFORMER SITAS; PHASES:1; PN/PN(S6)(KVA):0,315 /1,12;
UPRI(V):230+/-5%; USEC(V):110; ISEC(A):2,86; F(HZ):50...60;
VECTOR GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP00; TYPE
OF TERMINALS:SCREW/TAB CONNECTION;
INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4 >UL/CSA-
RECOGNIZED< >CONTROL CIRCUIT TRANSFORMER<
>ISOLATION TRANSFORMER<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	315
efficiency		0.9
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	1 120
relative short-circuit voltage	%	5.93
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	242
• _2 rated value	V	230
• _3 rated value	V	218
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	110
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
fastening method		screws

construction form of the iron core		EI 105/60
width	m	0.107
height	m	0.111
depth	m	0.12

Certificates/ approvals

General Product Approval	Declaration of Conformity	Marine / Shipping	other
--------------------------	---------------------------	-------------------	-------



[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM4342-4TJ10-0FA0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM4342-4TJ10-0FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM4342-4TJ10-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM4342-4TJ10-0FA0&lang=en

last modified:

2/12/2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[4AM43424TJ100FA0](#)