



Figure similar

TRANSFORMER SITAS; PHASES:1; PN/PN(S6)(KVA):5,6 /24,5; UPRI(V):550-525-500-480-460- 440-415-400-380-230-208; USEC(V):2X115; ISEC(A):2X24,4; F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; TA/ISOKL:55 /H; IP23; TYPE OF TERMINALS:SCREW CONNECTION; INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4 >UL/CSA-RECOGNIZED< >CONTROL CIRCUIT TRANSFORMER< >ISOLATION TRANSFORMER<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	5 600
efficiency		0.94
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	24 500
relative short-circuit voltage	%	3.2
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	550
• _2 rated value	V	525
• _3 rated value	V	500
• _4 rated value	V	480
• _5 rated value	V	460
• _6 rated value	V	440
• _7 rated value	V	415
• _8 rated value	V	400
• _9 rated value	V	380
• _10 rated value	V	230
• _11 rated value	V	208
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	230
• _2 rated value	V	115
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions		
thermal class according to IEC 60085		H
ambient temperature rated value	°C	55
protection class IP		IP23
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals
• at input for main current circuit		screw-type terminals
fastening method		screws
construction form of the iron core		UI 180/75
width	m	0.351
height	m	0.395
depth	m	0.33
Certificates/ approvals		
General Product Ap- proval	Declaration of Conformity	Marine / Shipping
		other



[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AT3632-8DD40-0FC0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AT3632-8DD40-0FC0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AT3632-8DD40-0FC0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AT3632-8DD40-0FC0&lang=en

last modified:

9/6/2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[4AT36328DD400FC0](#)