



LOGO! AM2 RTD expansion module, PS: 12/24 V DC, 2AI-50...+200°C
Pt100/1000 for LOGO! 8

Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 12 V DC	Yes; 10.8 V DC to 28.8 V DC
• 24 V DC	Yes; 10.8 V DC to 28.8 V DC
Input current	
Current consumption, typ.	30 mA
Analog inputs	
Number of analog inputs	2; 2 or 3 wire connection
Input ranges	
• Voltage	No
• Current	No
• Resistance thermometer	Yes; For PT100/PT1000 sensors
Input ranges (rated values), voltages	
• 0 to +10 V	No
Input ranges (rated values), currents	
• 0 to 20 mA	No
Input ranges (rated values), resistance thermometer	
• Pt 100	Yes
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C; ES03 and higher: -20 °C
• max.	55 °C
Dimensions	
Width	35.5 mm
Height	90 mm
Depth	58 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ED10551MD000BA2](#)