

LOGO! TD text display, 6-line, 3 background colors, 2 Ethernet ports, installation accessories for LOGO! 8



Figure similar

General information	
Product type designation	Text display
Suitability for use	Can be used with LOGO! 8 and higher
Display	
Design of display	FSTN
Line display	
• Number of lines	6
• Number of characters per line	20
Backlighting	
• Type of backlighting	LED
Control elements	
Keyboard fonts	
• System keys	Yes
— Number of configurable system keys	0
• alphanumeric keyboard	No
Installation type/mounting	
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	AC/DC
Rated value (DC)	12 V; 12/24 V DC, 24 V AC
Power loss	
Power loss, typ.	1.8 W; At 24 V DC
Interrupts/diagnostics/status information	
Diagnostics function	No
Degree and class of protection	
IP (at the front)	IP65
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
FM approval	Yes
KC approval	Yes
Marine approval	
• American Bureau of Shipping (ABS)	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	-20 °C; No condensation
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-40 °C

• max.	70 °C
Altitude during operation relating to sea level	
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)
<b>configuration / header</b>	
Configuration software	
• Configuration tool	LOGO! Soft Comfort V8
<b>Accessories</b>	
belongs to product	LOGO!
<b>Mechanics/material</b>	
Design of housing	plastic
<b>Dimensions</b>	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Overall depth	38.7 mm
<b>Weights</b>	
Weight, approx.	220 g
<b>Scope of supply</b>	
Delivery quantity in pieces	1

**last modified:** 2/26/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ED10554MH080BA1](#)