

### product type designation

### IWLAN RCoax connector N-Connect Female N-Connector

RCoax N-Connect female N-connector 2.4 and 5 GHz Can be assembled in the field; Connection piece of RCoax Cable for connection of further components.



electrical data	
number of electrical connections	1
type of electrical connection	N-Connect female
transmission frequency	0 ... 6 GHz
impedance	50 Ω
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
protection class IP	IP67
design, dimensions and weights	
diameter	27 mm
length	65 mm
net weight	159 g
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
further information / internet links	
internet link	
• to website: TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
• to the website: IWLAN	<a href="http://www.siemens.com/iwlan">http://www.siemens.com/iwlan</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Selection guide for cables and connectors	<a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

### last modified:

5/20/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57980CN000AA0