

product type designation

IWLAN Power Splitter N-Connect Female

N-Connect female power splitter 2-fold; 2.4 and 5 GHz Y-element.



electrical data

number of electrical connections	3
type of electrical connection	N-Connect female
transmission frequency	2.4 ... 6 GHz
impedance	50 Ω
return loss / minimum	24 dB
insertion loss / maximum	3.05 dB

ambient conditions

ambient temperature	
• during operation	-40 ... +110 °C
• during storage	-40 ... +110 °C
• during transport	-40 ... +110 °C
resistance to salt-laden atmosphere / conformity according to EN 60068-2-52	Yes; Severity 3
protection class IP	IP66/68; IP 68 at 0,5 bar/ 1 h

design, dimensions and weights

width	71.4 mm
length	131.4 mm
net weight	937 g

standards, specifications, approvals

certificate of suitability	
• RoHS conformity	Yes

further information / internet links

internet link	
• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/snst
• to the website: IWLAN	http://www.siemens.com/iwlan
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/20/2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK57980SN000EA0