



SCALANCE CLP 2GB W700 AP iFeatures. Removable data storage medium to activate iFeatures and supplementary functions in SCALANCE W access points and clients. can be used for easy device replacement in case of fault, for holding configuration data, can be used in the following products with CLP slot: SCALANCE W700 higher than or equal to W-Fi 5.

suitability for operation	SCALANCE W17xx devices
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
width	17.5 mm
height	7 mm
depth	32 mm
net weight	3.1 g
product feature / conformal coating	No
product features, product functions, product components / general	
storage capacity	2048 Mibyte
standards, specifications, approvals	
MTBF	343 a
• range of validity	At 25 °C
further information / internet links	
internet link	
• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/snst
• to the website: IWLAN	http://www.siemens.com/iwlan
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 5/28/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6GK59078UA000AA0