

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BB21-5BV1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

Input

Number of phases	1 AC
Line voltage	200 ... 240 V -15 % +10 %
Line frequency	47 ... 63 Hz

Output

Number of phases	3 AC	
Rated voltage	230V IEC	240V NEC 1)
Rated power (LO)	1.50 kW	2.00 hp
Rated power (HO)	1.50 kW	2.00 hp
Rated current (LO)	7.80 A	7.80 A
Rated current (HO)	7.80 A	7.80 A
Rated current (IN)	7.80 A	
Pulse frequency	8.00 kHz	
Output frequency	0 ... 550 Hz	

Overload capability

Low Overload (LO)
110 % rated output current for 60 s, cycle time 300 s
High Overload (HO)
150 % rated output current for 60 s, cycle time 300 s

General tech. specifications

Power factor λ	0.72
Offset factor $\cos \varphi$	0.95
Efficiency η	0.98
Filter class (integrated)	Class B

Communication

Communication	USS, Modbus RTU
---------------	-----------------

Inputs / outputs

Standard digital inputs

Number	4
--------	---

Digital outputs

Number as relay changeover contact	1
Number as transistor	1

Analog inputs

Number	2 (Can be used as additional digital input)
--------	---

Analog outputs

Number	1
--------	---

Ambient conditions

Cooling	External fan
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation ²⁾	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity

Max. operation	95 %
----------------	------

Connections

Max. motor cable length

Shielded	25 m (82.02 ft)
Unshielded	50 m (164.04 ft)

Mechanical data

Mounting position	Wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Frame size	FSAC
Net weight	1.40 kg (3.09 lb)

Dimensions

Width	91.0 mm (3.57 in)
Height	160.9 mm (6.33 in)
Depth	147.0 mm (5.79 in)

Standards

Compliance with standards	CE, cULus, C-Tick (RCM)
CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

¹⁾The output current and HP ratings are valid for the voltage range 220V-240V

²⁾Please observe derating at temperatures of 40 °C or above

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6SL32105BB215BV1](#)