

Data sheet for Smart Access Module

Article No. : 6SL3255-0VA00-5AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Electrical data	
Operating voltage (DC)	24 V
Rated data	
Operating frequency	2,400.0 ... 2,483.5 MHz
Damping factor per length (2.4 GHz), max.	17 dB/m
Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	28 g (0.99 oz)
Communication	
Wi-fi compatible	Yes
IEEE 802.11b	Yes
IEEE 802.11g	Yes
Ambient conditions	
Ambient temperature during	
Operation	0 ... 50 °C (32 ... 122 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Relative humidity	
without condensation	95 %
Standards	
Compliance with standards	CE / FCC / SRRC / WPC / TRA / CNC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6SL32550VA005AA0](#)