

Data sheet for I/O extension module

Article No. : 6SL3256-0VE00-6AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Inputs / outputs	
Digital inputs	
Number of digital inputs ¹⁾	2
Conductor cross-section	0.20 ... 0.75 mm² (AWG 22 ... AWG 18)
Input voltage (0→1)	11 V
Input voltage (1→0)	5 V
Input voltage, max.	30 V
Digital outputs	
Number of digital outputs	2
Conductor cross-section	0.75 mm² (AWG 18)
Output current ²⁾	0.5 A

Mechanical data	
Dimensions	
Width	57 mm (2.25 in)
Height	90 mm (3.54 in)
Depth	33 mm (1.29 in)

¹⁾DI 5, DI 6: digital input
²⁾DO3, DO4 digital relay output, resistive load 0.5A at 250 V AC; 0.5A at 30 V DC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6SL32560VE006AA0](#)