

product type designation

product description

Cable 830-1T

Plug-in cable, preferred length, preassembled with two 9-pole D-sub connectors

Plug-in cable 830-1T for PROFIBUS for connection of terminal devices to OLM and OBT Already pre-assembled with 2 D-sub connectors, 9-pole, cable terminated on both ends, 3 m.



suitability for use

For connecting PROFIBUS stations to OLM or OBT

cable designation

L-02YSCY 1x2x0,22 VZN VI

wire length

3 m

electrical data

number of electrical connections

2

insulation resistance coefficient

1 GΩ·m

capacity per length / at 1 kHz

30 pF/m

operating voltage

• RMS value

80 V

mechanical data

number of electrical cores

2

design of the shield

Braided shield made of tin-plated copper wires

outer diameter

• of inner conductor

0.61 mm

• of the wire insulation

1.8 mm

• of cable sheath

5.7 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

• of the wire insulation

polyethylene (PE)

• of cable sheath

PVC

color

• of cable sheath

Violet

bending radius

• with multiple bends / minimum permissible

86 mm

ambient conditions

ambient temperature

• during operation

-40 ... +70 °C

• during storage

-40 ... +70 °C

• during transport

-40 ... +70 °C

fire behavior

flame resistant according to IEC 60332-1

chemical resistance

• to mineral oil

oil resistant according to IEC 60811-2-1 (4 h / 70°C)

protection class IP

IP20

product features, product functions, product components / general

product feature

• silicon-free

Yes

standards, specifications, approvals

certificate of suitability

• EAC approval	Yes
• CE marking	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB

further information / internet links

internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

12/31/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

6XV18301CH30