



Extension shaft 600 mm, 8x 8 mm Accessory for: Door-coupling rotary mechanism and Side rotary operating mechanism 3VA

Model		
product brand name	SETRON	
product designation	extension shaft	
length of shaft of door-coupling rotary operating mechanism	600 mm	
suitability for use	for door mounted rotary operator and side mounted operator	
Product details		
product description	600 mm	
product component <ul style="list-style-type: none">extension shaft	Yes	
Mechanical Design		
net weight	266 g	
General Product Approval	Declaration of Conformity	Marine / Shipping



other	Environment
-------	-------------

[Confirmation](#)

[Miscellaneous](#)

[Environmental Con-
firmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8UD1900-2WB00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8UD1900-2WB00>


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8UD1900-2WB00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications



last modified:

7/29/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8UD19002WB00