



Integrated signal lamp, rotating light, with integrated LED, yellow, 24 V AC/DC, Diameter 70 mm

General technical data		
product designation	Rotating light element	
consumed current maximum	40 mA	
type of voltage of the operating voltage	AC/DC	
operating voltage		
• 1 at DC rated value	24 V	
• 1 at AC at 50 Hz rated value	24 V	
• 1 at AC at 60 Hz rated value	24 V	
relative positive tolerance of the operating voltage	10 %	
relative negative tolerance of the operating voltage	-10 %	
speed	120 1/min	
reference code according to IEC 81346-2	P	
fastening method	Bayonet / flush mounting	
material	PC; PC/ABS; PA	
color	yellow	
Mechanical data		
product component light source	Yes	
type of electrical connection	screw-type terminals	
outer diameter of the signal column element	75 mm	
Lamp		
design of the optical signal	rotating light	
type of light source	LED	
light intensity	3.3 cd	
service life of LED	100 000 h	
Ambient conditions		
ambient temperature during operation	-20 ... +50 °C	
protection class IP	IP65	
depth	31 mm	
height	66 mm	
width	75 mm	
Certificates/ approvals		
General Product Approval	EMC	Declaration of Conformity

[Confirmation](#)



other

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5320-5DD>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5320-5DD>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5320-5DD>


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5320-5DD&lang=en





last modified:

12/21/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8WD53205DD