



Integrated signal lamp, single flash light, w. built-in electronic flash, blue, 115 V AC, Diameter 70 mm

General technical data		
product designation	Flashlight element	
consumed current maximum	22 mA	
type of voltage of the operating voltage	AC	
operating voltage		
• 1 at AC at 50 Hz rated value	115 V	
• 1 at AC at 60 Hz rated value	115 V	
relative positive tolerance of the operating voltage	10 %	
relative negative tolerance of the operating voltage	-10 %	
reference code according to IEC 81346-2	P	
fastening method	Bayonet / flush mounting	
material	PC; PC/ABS; PA	
color	blue	
Mechanical data		
product component light source	Yes	
type of electrical connection	screw-type terminals	
outer diameter of the signal column element	75 mm	
Lamp		
design of the optical signal	flash light	
type of light source	Xenon gas discharge lamp	
light intensity	16 317 cd	
flash frequency	1 Hz	
number of flashes of light element	4 000 000	
Ambient conditions		
ambient temperature during operation	-20 ... +50 °C	
protection class IP	IP65	
depth	31 mm	
height	66 mm	
width	75 mm	
Certificates/ approvals		
General Product Approval	EMC	Declaration of Conformity

[Confirmation](#)



other

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5340-0CF>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5340-0CF>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5340-0CF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5340-0CF&lang=en





last modified:

12/23/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8WD53400CF