



Breaker BQD 2P 100A 480V AC 14kA

General technical data	
number of poles	2
suitability for operation	CONSTRUCTION
Electricity	
continuous current rated value	100 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	40 °C
Model	
product brand name	SIEMENS
special product feature	PANELBOARD MOUNT
type of electrical connection	LOW TAB
Mechanical Design	
depth [in]	4 in
design of the overload release	THERMAL MAGNETIC TRIP UNIT
design of the product	BQD
height [in]	2 in
material of the enclosure	MOLDED CASE CIRCUIT BREAKER
size of the circuit-breaker	100A
width [in]	3 in
General product approval	
standard	UL 489 CSA-C22.2

last modified:

12/21/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[BQD2100](#)