

BREAKER BQD 3P 40A 480VAC 14KA 120V STW/120V S.T., FACTORY
INSTALLED

General technical data	
number of poles	3
suitability for operation	CONSTRUCTION
Electricity	
continuous current rated value	40 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	40 °C
Model	
product brand name	SIEMENS
special product feature	PANELBOARD MOUNT, 120/240 VACSHUNT TRIP
type of electrical connection	LOW TAB
Mechanical Design	
depth [in]	0 in
design of the overload release	THERMAL MAGNETIC TRIP UNIT
design of the product	BQD
height [in]	0 in
material of the enclosure	MOLDED CASE CIRCUIT BREAKER
size of the circuit-breaker	100A
width [in]	0 in
General product approval	
standard	UL 489 CSA-C22.2

last modified:

10/24/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[BQD34000S01](#)